

Master M WorkPack 1-MIG - programmi di saldatura standard in mastermig 353

PANORAMICA

PACCHETTO WORK PACK CON PROGRAMMI DI SALDATURA INSTALLATO IN FABBRICA PER MASTERMIG 353.

Codice	Descrizione
MSM10000	MSM A01 1-MIG AlMg5 1.0mm Ar
MSM10001	MSM A02 1-MIG AlMg5 1.2mm Ar
MSM10002	MSM A11 1-MIG AlSi5 1.0mm Ar
MSM10003	MSM A12 1-MIG AlSi5 1.2mm Ar
MSM10004	MSM C01 1-MIG CuSi3 0.8mm Ar
MSM10005	MSM C03 1-MIG CuSi3 1.0mm Ar
MSM10006	MSM C11 1-MIG CuAl8 0.8mm Ar
MSM10007	MSM C13 1-MIG CuAl8 1.0mm Ar
MSM10008	MSM F01 1-MIG Fe 0.8mm Ar + 18%CO2
MSM10009	MSM F02 1-MIG Fe 0.9mm Ar + 18%CO2
MSM10010	MSM F03 1-MIG Fe 1.0mm Ar + 18%CO2
MSM10011	MSM F04 1-MIG Fe 1.2mm Ar + 18%CO2
MSM10012	MSM F11 1-MIG Fe 0.8mm Ar + 8%CO2
MSM10013	MSM F12 1-MIG Fe 0.9mm Ar + 8%CO2
MSM10014	MSM F13 1-MIG Fe 1.0mm Ar + 8%CO2
MSM10015	MSM F14 1-MIG Fe 1.2mm Ar + 8%CO2
MSM10016	MSM F21 1-MIG Fe 0.8mm CO2
MSM10017	MSM F22 1-MIG Fe 0.9mm CO2
MSM10018	MSM F23 1-MIG Fe 1.0mm CO2
MSM10019	MSM F24 1-MIG Fe 1.2mm CO2
MSM10020	MSM M04 1-MIG Fe Metal 1.2mm Ar + 18%CO2
MSM10021	MSM R04 1-MIG Fe Rutil 1.2mm Ar + 18%CO2
MSM10022	MSM S01 1-MIG CrNiMo 19 12 0.8mm Ar + 2%CO2
MSM10023	MSM S02 1-MIG CrNiMo 19 12 0.9mm Ar + 2%CO2
MSM10024	MSM S03 1-MIG CrNiMo 19 12 1.0mm Ar + 2%CO2
MSM10025	MSM S04 1-MIG CrNiMo 19 12 1.2mm Ar + 2%CO2
MSM10026	MSM S82 1-MIG FC-CrNiMo 19 12 0.9mm Ar + 18%CO2
MSM10027	MSM S84 1-MIG FC-CrNiMo 19 12 1.2mm Ar + 18%CO2

SPECIFICHE TECNICHE

Master M WorkPack 1-MIG - Programmi di saldatura standard in MasterMig 353

Codice prodotto	MSM350100
Descrizione	Programmi di saldatura standard in MasterMig 353