

Master M WorkPack 1-MIG - standard sveiseprogram til master m 353.

OVERSIKT

FABRIKK INSTALLERT WORK PACK SVEISEPROGRAM FOR MASTER M 353.

| Kode | Beskrivelse |
|----------|---|
| MSM10000 | MSM A01 1-MIG AlMg5 1.0mm Ar |
| MSM10001 | MSM A02 1-MIG AlMg5 1.2mm Ar |
| MSM10002 | MSM A11 1-MIG AlSi5 1.0mm Ar |
| MSM10003 | MSM A12 1-MIG AlSi5 1.2mm Ar |
| MSM10004 | MSM C01 1-MIG CuSi3 0.8mm Ar |
| MSM10005 | MSM C03 1-MIG CuSi3 1.0mm Ar |
| MSM10006 | MSM C11 1-MIG CuAl8 0.8mm Ar |
| MSM10007 | MSM C13 1-MIG CuAl8 1.0mm Ar |
| MSM10008 | MSM F01 1-MIG Fe 0.8mm Ar + 18%CO2 |
| MSM10009 | MSM F02 1-MIG Fe 0.9mm Ar + 18%CO2 |
| MSM10010 | MSM F03 1-MIG Fe 1.0mm Ar + 18%CO2 |
| MSM10011 | MSM F04 1-MIG Fe 1.2mm Ar + 18%CO2 |
| MSM10012 | MSM F11 1-MIG Fe 0.8mm Ar + 8%CO2 |
| MSM10013 | MSM F12 1-MIG Fe 0.9mm Ar + 8%CO2 |
| MSM10014 | MSM F13 1-MIG Fe 1.0mm Ar + 8%CO2 |
| MSM10015 | MSM F14 1-MIG Fe 1.2mm Ar + 8%CO2 |
| MSM10016 | MSM F21 1-MIG Fe 0.8mm CO2 |
| MSM10017 | MSM F22 1-MIG Fe 0.9mm CO2 |
| MSM10018 | MSM F23 1-MIG Fe 1.0mm CO2 |
| MSM10019 | MSM F24 1-MIG Fe 1.2mm CO2 |
| MSM10020 | MSM M04 1-MIG Fe Metal 1.2mm Ar + 18%CO2 |
| MSM10021 | MSM R04 1-MIG Fe Rutil 1.2mm Ar + 18%CO2 |
| MSM10022 | MSM S01 1-MIG CrNiMo 19 12 0.8mm Ar + 2%CO2 |
| MSM10023 | MSM S02 1-MIG CrNiMo 19 12 0.9mm Ar + 2%CO2 |
| MSM10024 | MSM S03 1-MIG CrNiMo 19 12 1.0mm Ar + 2%CO2 |
| MSM10025 | MSM S04 1-MIG CrNiMo 19 12 1.2mm Ar + 2%CO2 |
| MSM10026 | MSM S82 1-MIG FC-CrNiMo 19 12 0.9mm Ar + 18%CO2 |
| MSM10027 | MSM S84 1-MIG FC-CrNiMo 19 12 1.2mm Ar + 18%CO2 |

TEKNISKE SPESIFIKASJONER

Master M WorkPack 1-MIG - Standard sveiseprogram til Master M 353.

| | |
|-------------|--|
| Produktkode | MSM350100 |
| Beskrivelse | Standard sveiseprogram til Master M 353. |